

**CUSH-2-58-158**

Cushion with 2 Holes, for 20-22mm Cables, Compatible with 1-5/8" Clamps

The multi-hole cushions are available in various combinations of hole sizes and quantities. This unique design allows using a single cushion to easily manage and fix multiple cables of different sizes. Multi-hole cushions can be installed using popular cable clamps, including snap-in, butterfly, stackable clamps, and cable blocks. The hanger solutions with these multi-hole cushions are very useful in the tower-top cable management for the installation of AISG, fiber, power, hybrid, and coaxial cables with an outer diameter up to 5/8".

FEATURES / BENEFITS

- One cushion accommodates multiple cables in different sizes - reduce material and installation costs, save spaces on tower
- Made of UV-resistant EPDM - solution is durable even in extreme environmental conditions
- Versatile design - Fix and manage various cables by one cushion
- Compatible to various types of clamps - support diverse site conditions

**Technical features****GENERAL SPECIFICATIONS**

Product Type		Rubber Cushion, Cable Lining
Configuration		Multi-hole
Color		Black
Installation Hardware Type		Snap-in Clamp, Stackable Snap-in Clamp, Butterfly Clamp, Clip-on Clamp, Cable block
Compatible Clamp Size	in	1-5/8"

MECHANICAL SPECIFICATIONS

Material		EPDM Rubber
Number of Cable / Waveguide Runs		2
Amount of Hole Type 1		2

TEMPERATURE SPECIFICATIONS

Installation Temperature	°C (°F)	0 to 30 (32 to 86)
Operation Temperature	°C (°F)	-25 to 75 (-13 to 167)
Storage Temperature	°C (°F)	-10 to 25 (14 to 77)

PACKAGING INFORMATION

Package Quantity		10
Weight per kit	kg (lb)	1 (2.2)



CUSH-2-58-158

Cushion with 2 Holes, for 20-22mm Cables, Compatible with 1-5/8" Clamps

RELATED PRODUCTS

MULTI-HOLE CUSHION SPECIFICATIONS				COMPATIBLE CLAMP OPTIONS (CLICK MODELS TO SEE DATASHEETS)		
Model Number	Total Hole Quantity	Cable 1 Quantity x Size Range	Cable 2 Quantity x Size Range	Stackable Snap-in Clamp	Snap-in Clamp	Butterfly Clamp
CUSH-4-L12-158	4	4 x 15 - 17 mm	N/A	SNAP-ST-158	SNAP-158	CLAMP-158
CUSH-4-S14-2-L12-158	6	4 x 6 - 7 mm	2 x 15 - 17 mm			
CUSH-4-L1438-2-L12-158	6	4 x 10 - 11 mm	2 x 15 - 17 mm			
CUSH-4-S14-4-L14S12-158	8	4 x 6 - 7 mm	4 x 11 - 13 mm			
CUSH-1-L1438-2-58-158	3	1 x 10 - 11 mm	2 x 19 - 21 mm			
CUSH-10-S14-158	10	10 x 5 - 7 mm	N/A			
CUSH-4-S14-4-L1438-158	8	4 x 6 - 7 mm	4 x 9 - 11 mm			
CUSH-4-S14-2-58-158	6	4 x 6 - 7 mm	2 x 20- 22 mm			
CUSH-7-L14S38-158	7	7 x 9 - 10 mm	N/A			
CUSH-2-58-158	2	2 x 20- 22 mm	N/A			
CUSH-7-14S38-158	7	7 x 4-10 mm	N/A			

* More cushions and clamps may be available upon request.

External Document Links
Installation Instruction

Notes